

SIMATIC S7-400，组件支架 UR1，中央式的和分布式的 带有 18 个插槽 2 个冗余电源连接器



一般信息			
产品类型标志		UR1	
硬件扩展			
组件载体			
● K 总线		是	
● P 总线		是	
插槽			
● 插槽数量		18	
标准、许可、证书			
CE 标记		是	
UKCA 标志		是	
UL 许可		是	
FM 许可		是	
RCM（原 C-TICK）		是	
KC 许可		是	
EAC（原 Gost-R）		是	
CCC		是	
环境要求			
运行中的环境温度			
● 最小值		0 °C	
● 最大值		60 °C	
运输/储存时的环境温度			
● 最小值		0 °C	
● 最大值		70 °C	
尺寸			
宽度		482.5 mm	
高度		290 mm	
深度		27.5 mm	
重量			
重量，约		4.1 kg	
分类			
		版本	分类
	eClass	14	27-24-22-03
	eClass	12	27-24-22-03

eClass	9.1	27-24-22-03
eClass	9	27-24-22-03
eClass	8	27-24-22-03
eClass	7.1	27-24-22-03
eClass	6	27-24-22-03
ETIM	10	EC000810
ETIM	9	EC000810
ETIM	8	EC000810
ETIM	7	EC000810
IDEA	4	3560
UNSPSC	15	32-15-17-04

认可 / 证书

General Product Approval



[Manufacturer Declaration](#)

[Miscellaneous](#)



[China RoHS](#)



General Product Approval EMV For use in hazardous locations

[KC](#)



For use in hazardous locations

[Declaration of Conformity](#)

[FM](#)



[Type Examination Certificate](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application Environment



[CCS \(China Classification Society\)](#)



上一次修改：2025/6/7