








RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1.0A/contact terminal
2. 额定电压: Voltage Rating 30V DC
3. 接触电阻: Contact Resistance 50 milliohms MAX
4. 耐压: Dielectric Withstanding Voltage: 300 V AC AT Sea Level
5. 绝缘电阻: Insulation Resistance: 100MEGA ohms MIN

原材料: Raw material:

1. 塑胶: Plastic cement:
High Temperature Thermoplastics,
LCP Black
 2. 端子: Contact: Copper Alloy C2680/C5191
 3. 外壳: Shell: SPCC/Copper Alloy C2680
- 电镀: Electroplate:
1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails
 2. 外壳: Shell:
Nickel Plating

DIMENSION IN mm		厦门市辛译精密电子有限公司			
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyconn Electronics Co.,Ltd			
.X±0.35	X* ± 5°	APR.	Alex	TITLE: MINI USB 5P/F SMT B#(0.3T, 0.6#)	
.XX±0.25	.X* ± 3°	CHK.	Jack	DWG NO. XY-5PTP-MINIUSB	
.XXX±0.15	.XX* ± 1°	DRA.	Can	PROJ. 	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1