





SPECIFICATION:


- Material & Finish: See the list;
- Mechanical:
 - Mating force: 5-20Nf;
 - Unmating force: 6-20Nf;
 - Durability: 3000 Cycles;
- Electrical:
 - Current Rating: 3A Max.;
 - Voltage Rating: 20V Max.;
 - Dielectric Withstanding voltage: 100Vac;
 - Contact resistance: 40m Ohms Max.;
 - Insulation Resistance: 100M Ohms Min.;
- Environmental:
 - Operating temperature: -40°C~+85°C;
 - Salt Spray Test: 24H Min. (No oxidation or rust);
 - Wetting Temperature: 265±5°C, 5±0.5s

A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL	PIN	SIGNAL




NO.	PART NAME	Q'TY	MATERIAL	FINISH
3	Shell	1	SUS201 T=0.30mm	Ni
2	Housing	1	LCP	UL 94 V-0
1	Contact	1	C5191 T=0.20mm	Au

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*±3	APR. Alex	TITLE: TYPE-C 6Pin 间距6.80mm SMT		
.XX±0.25	.X*±2	CHK. Jack	DWG NO. XY-TYPEC-6PIN		
.XXX±0.15	.XX*±	DRA. Can	PROJ. 	CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1



NO.	NAME	SPEC	Q'TY
①	TYPE C RECEPTACLE		15000PCS/CARTON
②	CARRIER TAPE	W=16mm,T=0.40mm	1000PCS/PLATE
③	COVER TAPE	W=13.2mm	15PLATES/CARTON
④	REEL PLATE	$\phi 330*100*16.4$ mm	15PCS/CARTON
⑤	RoHS LABEL		15PCS/CARTON
⑥	PRODUCT LABER		15PCS/CARTON
⑦	CARTON	340*340*325mm	1PCS/PACKAGE



说明:

- 每卷前后各空16PCS,尾部用美纹纸封住;
- 将产品放满盘后,再卷一圈保护带,用美纹纸将其封住,并贴上1Pcs物料标签;
- 每15卷盘一叠共15000Pcs装入1个外箱内;
- 在搬运过程中要轻拿轻放;
- 在运输中不可堆放过多(1.8M最高),不可重压;
- 跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a. 产品不可跑出下带凹槽;
b. 产品不可有划伤,变形;
c. 内包装材料不可严重破损。

DIMENSION IN mm		厦门市辛译精密电子有限公司					
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyeconn Electronics Co.,Ltd					
.X±0.35	X:± 3	APR.	Alex	TITLE: TYPE-C 6Pin 间距6.80mm SMT			
.XX±0.25	.X*± 2	CHK.	Jack	DWG NO. XY-TYPEC-6PIN			
.XXX±0.15	.XX*±			PROJ.		CUSTOMER DRAWING	
			Can	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A