




标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

PIN	尺寸 (mm)		
	A	B	C
02	2.54	5.08	2.25
03	5.08	7.62	4.79
04	7.62	10.16	7.33
05	10.16	12.70	9.87
06	12.70	15.24	12.41
07	15.24	17.78	14.95
08	17.78	20.32	17.49
09	20.32	22.86	20.03
10	22.86	25.40	22.57
11	25.40	27.94	25.11
12	27.94	30.48	27.65
13	30.48	33.02	30.19
14	33.02	35.56	32.73
15	35.56	38.10	35.27
16	38.10	40.64	37.81

SPECIFICATIONS

- 1.Current Rating: 4A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Wafer Nylon66
PIN Brass Tin-plated

2	插针	铜	镀锡	
1	基座	PA66	米色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	针座	
			料 号 PART NO	HC-XH2510-3AW-M	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X.±0.25 X.*±2'		单 位 UNIT	MM	制 图 DRAW	AhYe
.X±0.20 .X*±1'		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.15 .XX*±0.5'		版 本 REV	A	批 准 APPROVE	赵亮亮
.XXX±0.10 .XXX*±0.5'					

PCB LAYOUT