




http://hcdz2017.com/

2

3

4

5

6

7

8

9

标 记
MARK

ECN编号/变更内容
ECN NO/DEFINITION

修 改
REVISE

日 期
DATE

核 准
APPROVE

编号

尺寸 (mm)

A

B

02Y

2.54

5.68

03Y

5.08

8.22

04Y

7.62

10.76

05Y

10.16

13.30

06Y

12.70

15.84

07Y

15.24

18.38

08Y

17.78

20.92

09Y

20.32

23.46

10Y

22.86

26.00

11Y

25.40

28.54

12Y


27.94

31.08

SPECIFICATIONS

- 1.Current Rating: 4A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25℃~+85℃
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Nylon66

1	胶壳	PA66	白色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	胶壳	
			料 号 PART NO	HC-JK-XH2510-7Y	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X.±0.25	X'±2'	单 位 UNIT	MM	制 图 DRAW	AhYe
.X±0.20	.X'±1'	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.15	.XX'±0.5'	版 本 REV	A	批 准 APPROVE	赵亮亮
.XXX±0.10	.XXX'±0.5'				

http://hcdz2017.com/