

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN

尺寸 (mm)

A

B

C

02

2.50

7.40

6.50

03

5.00

9.90

9.00

04

7.50

12.40

11.50

05

10.00

14.90

14.00

06

12.50

17.40

16.50

07

15.00

19.90

19.00

08

17.50

22.40

21.50

09

20.00

24.90

24.00

10







22.50

27.40

26.50

SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Wafer PA66
PIN Brass Tin-plated



深圳市虹成电子有限公司

GENERAL TOLERANCES
(UNLESS SPECIFIED)

X:±0.25 X:±2°

.X:±0.25 .X:±1°

.XX:±0.15 .XX:±0.5°

.XXX:±0.10 .XXX:±0.5°

比 例
SCALE

1:1

单 位
UNIT

MM

张 数
PART NO

1 OF 1

版 本
REV

A

制 图
DRAW

AhYe

审 核
CHECKED

夏操云

批 准
APPROVE

赵亮亮

