

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

编号

尺寸 (mm)

A

B

2*02A

2.50

7.50

2*03A

5.00

10.00

2*04A

7.50

12.50

2*05A

10.00

15.00

2*06A

12.50

17.50

2*07A

15.00

20.00

2*08A

17.50

22.50

2*09A

20.00

25.00

2*10A

22.50

27.50

2*11A





25.00

30.00

2*12A



27.50

32.50



SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25℃~+85℃
- 4.Contact Resistance: 30mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 800V AC/minute
- 7.Material: Wafer PA66.Beige
PIN Brass Tin-plated



2	插针	铜	镀锡	
1	基座	PA66	米色	
序号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-XHD2.54-2x8AW

GENERAL TOLERANCES
(UNLESS SPECIFIED)

比 列
SCALE

1:1



X.X±0.25 X.±2°

单 位
UNIT

MM

制 图
DRAW

AhYe

X.XX±0.20

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

X.XXX±0.10

版 本
REV

A

批 准
APPROVE

赵亮亮

