




标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

编号	尺寸 (mm)	
	A	B
2A	2.50	7.50
3A	5.00	10.00
4A	7.50	12.50
5A	10.00	15.00
6A	12.50	17.50
7A	15.00	20.00
8A	17.50	22.50
9A	20.00	25.00
10A	22.50	27.50
11A	25.00	30.00
12A	27.50	32.50

SPECIFICATIONS

1.Current Rating:3A AC, DC

2.Voltage Rating:250V AC, DC

3.Temperatuer Range:−25℃~+85℃

4.Contact Resistance:20mΩ Max


5.Insulation Resistance: 1000MΩ Min


6.Withstanding Voltang: 1000V AC/minute

7.Material:Wafer PA66

PIN Brass Tin-plated

2	插针	铜	镀锡	
1	基座	PA66	白色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE		针座	
			料 号 PART NO		5264-7A-TW	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1			
X.±0.25 X.±2'		单 位 UNIT	MM	制 图 DRAW	AhYe	
.X±0.20 .X'±1'		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
.XX±0.15 .XX'±0.5'		版 本 REV	A	批 准 APPROVE	赵亮亮	
.XXX±0.10 .XXX'±0.5'						



PCB LAYOUT