




http://hcdz2017.com/

2

3

4

5

6

7

8

9

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

编号	尺寸 (mm)	
	A	B
2X01		4.00
2X02	3.00	7.00
2X03	6.00	10.00
2X04	9.00	13.00
2X05	12.00	16.00
2X06	15.00	19.00
2X07	18.00	22.00
2X08	21.00	25.00
2X09	24.00	28.00
2X10	27.00	31.00
2X11	30.00	34.00
2X12	33.00	37.00

SPECIFICATIONS

1.Current Rating: 5A AC, DC

2.Voltage Rating: 250V AC, DC

3.Temperatuer Range: -25℃~+85℃

4.Contact Resistance: 20mΩ Max


5.Insulation Resistance: 1000MΩ Min

6.Withstanding Voltang: 1500V AC/minute

7.Material: Wafer PA66 Black

PIN Brass Tin-plated

2	插针	铜	镀锡	
1	胶壳	PA66	本色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE		胶壳	
			料 号 PART NO		HC-5557-MX3.0-2x9Y	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1			
X.±0.25 X'±2'		单 位 UNIT	MM	制 图 DRAW	AhYe	
.X±0.20 .X'±1'		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
.XX±0.15 .XX'±0.5'		版 本 REV	A	批 准 APPROVE	赵亮亮	
.XXX±0.10 .XXX'±0.5'						

http://hcdz2017.com/