





标记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修改 REVISE	日期 DATE	核准 APPROVE

PIN	尺寸 (mm)		
	A	B	C
02	2.54	5.08	2.25
03	5.08	7.62	4.79
04	7.62	10.16	7.33
05	10.16	12.70	9.87
06	12.70	15.24	12.41
07	15.24	17.78	14.95
08	17.78	20.32	17.49
09	20.32	22.86	20.03
10	22.86	25.40	22.57
11	25.40	27.94	25.11
12	27.94	30.48	27.65
13	30.48	33.02	30.19
14	33.02	35.56	32.73
15	35.56	38.10	35.27
16	38.10	40.64	37.81



- SPECIFICATIONS**
- 1.Current Rating: 4A AC, DC
 - 2.Voltage Rating: 250V AC, DC
 - 3.Temperatuer Range: -25°C~+85°C
 - 4.Contact Resistance: 20mΩ Max
 - 5.Insulation Resistance: 1000MΩ Min
 - 6.Withstanding Voltang: 1000V AC/minute
 - 7.Material: Wafer Nylon66
PIN Brass Tin-plated



2	插针	铜	镀锡	
1	基座	PA66	米色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品名 TITLE	针座	
			料号 PART NO	HC-XH2510-10A-M	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列 SCALE	1:1		
X±0.25	X'±2'	单位 UNIT	MM		
.X±0.20	.X'±1'	张数 PART NO	1 OF 1		
.XX±0.15	.XX'±0.5'	版本 REV	A		
.XXX±0.10	.XXX'±0.5'			制图 DRAW	AhYe
				审核 CHECKED	夏操云
				批准 APPROVE	赵亮亮