

| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|-------------|---------------------------------|---------------|-------------|----------------|
|             |                                 |               |             |                |
|             |                                 |               |             |                |

| PIN    | 尺寸 (mm) |       |
|--------|---------|-------|
|        | A       | B     |
| 2*04AW | 7.50    | 15.00 |
| 2*05AW | 10.00   | 17.50 |
| 2*06AW | 12.50   | 20.00 |
| 2*07AW | 15.00   | 22.50 |
| 2*08AW | 17.50   | 25.00 |
| 2*09AW | 20.00   | 27.50 |
| 2*10AW | 22.50   | 30.00 |
| 2*11AW | 25.00   | 32.50 |
| 2*12AW | 27.50   | 35.00 |
| 2*13AW | 30.00   | 37.50 |
| 2*14AW | 32.50   | 40.00 |
| 2*15AW | 35.00   | 42.50 |

A

B

C

D

E

F

G

A

B



C

D

E

F

G



SPECIFICATIONS

1.Current Rating:1A AC, DC

2.Voltage Rating:30V AC, DC

3.Temperatuer Range:−25℃~+85℃



4.Contact Resistance:30mΩ Max

5.Insulation Resistance: 100MΩ Min

6.Withstanding Voltang: 200V AC/minute


7.Material:Wafer PA66

PIN C2680 Tin-plated



PCB LAYOUT

|    |     |      |       |     |
|----|-----|------|-------|-----|
| 2  | 插针  | 铜    | 镀锡    |     |
| 1  | 基座  | PA66 | 米色    |     |
| 序号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |

|                                                                                                   |        |                |                 |                                                                                       |
|---------------------------------------------------------------------------------------------------|--------|----------------|-----------------|---------------------------------------------------------------------------------------|
|  深圳市虹成电子有限公司 |        | 品 名<br>TITLE   | 针座              |                                                                                       |
|                                                                                                   |        | 料 号<br>PART NO | HC-XA2.54-2X4AW |                                                                                       |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                                          |        | 比 列<br>SCALE   | 1:1             |  |
| X.X±0.25                                                                                          | X.*±2° | 单 位<br>UNIT    | MM              | 制 图<br>DRAW                                                                           |
| X.XX±0.20                                                                                         |        | 张 数<br>PART NO | 1 OF 1          | 审 核<br>CHECKED                                                                        |
| X.XXX±0.10                                                                                        |        | 版 本<br>REV     | A               | 批 准<br>APPROVE                                                                        |
|                                                                                                   |        |                |                 | 夏操云                                                                                   |
|                                                                                                   |        |                |                 | 赵亮亮                                                                                   |

