






编号

尺寸 (mm)

编号	A		B	
2*02Y	2.50		7.50	
2*03Y	5.00		10.00	
2*04Y	7.50		12.50	
2*05Y	10.00		15.00	
2*06Y	12.50		17.50	
2*07Y	15.00		20.00	
2*08Y	17.50		22.50	
2*09Y	20.00		25.00	
2*10Y	22.50		27.50	



SPECIFICATIONS

- 1.Current Rating:3A AC, DC
- 2.Voltage Rating:250V AC, DC
- 3.Temperatuer Range:−25°C~+85°C
- 4.Contact Resistance:30mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 800V AC/minute
- 7.Material:Housing PA66

1	胶壳	PA66	本色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品名 TITLE	胶壳
料号 PART NO	HC-XHD2.54-2x5Y

GENERAL TOLERANCES (UNLESS SPECIFIED)		比 例 SCALE	1:1	PART NO.		
X.X±0.25	X.±2°	单 位 UNIT	MM	制 图 DRAW	AhYe	
X.XX±0.20		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
X.XXX±0.10		版 本 REV	A	批 准 APPROVE	赵亮亮	

