

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN

尺寸 (mm)

A

B

C

D

02

0.80

3.04

3.80

1.90

03

1.60

3.84

4.60

2.70

04

2.40

4.64

5.40

3.50

05

3.20

5.44

6.20

4.30

06

4.00

6.24

7.00

5.10

07

4.80

7.04

7.80

5.90

08

5.60

7.84

8.60

6.70

09

6.40

8.64

9.40

7.50

10

7.20

9.44

10.2

8.30

技术要求:









额定电流: 0.7A AC,DC

额定电压: 30V AC

温度范围: -40° C~+85° C

接触电阻: $\leq 0.03 \Omega$ 绝缘电阻: $\geq 100M \Omega$

耐 压: 200V AC/min



PCB Layout

2	接触	铜	镀锡	
1	基座	LCP	米色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-SURO. 8-10PWT

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

单 位
UNIT

MM

制 图
DRAW审 核
CHECKED批 准
APPROVE

X.±0.30

X.±5°

.X±0.25

.X±3°

.XX±0.20

.XX±1°

张 数
PART NO

1 OF 1

版 本
REV

A

夏操云

赵亮亮

