





编号	尺寸 (mm)	
	A	B
2X1	— —	6. 10
2X2	3. 00	9. 10
2X3	6. 00	12. 10
2X4	9. 00	15. 10
2X5	12. 00	18. 10
2X6	15. 00	21. 10
2X7	18. 00	24. 10
2X8	21. 00	27. 10
2X9	24. 00	30. 10
2X10	27. 00	33. 10
2X11	30. 00	36. 10
2X12	33. 00	39. 10



- 1.Current Rating:5A AC, DC
- 2.Voltage Rating:250V AC, DC
- 3.Temperatuer Range:−25°C~+85°C
- 4.Contact Resistance:20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material:Wafer PA66 Black
PIN Brass Tin-plated

2	插针	铜	镀锡	
1	基座	PA66	黑色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE		针座	
			料 号 PART NO		HC-5557-MX3.0-2x2A	
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 例 SCALE	1 : 1		
X.±0.25 X'±2'			单 位 UNIT	MM	制 图 DRAW	AhYe
.X±0.25 .X'±1'			张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.15 .XX'±0.5'			版 本 REV	A	批 准 APPROVE	赵亮亮
.XXX±0.10 .XXX'±0.5'						

PCB LAYOUT