

说明:

1.材质:

胶芯:LCP,UL94V-0; COLOR; BLACK

端子:C2680

外壳:SPCC/C2680

2.电镀说明:

端子:接触区域镀金

焊锡区域镀锡100 u"Min

全部区域镀底50 u" Min

外壳:表面镀镍100 u" Min

3.电气性能:








绝缘阻抗(EIA-364-21):100 MΩ MIN.

AT 500V/DC FOR 1 MINUTE.

接触阻抗(EIA-364-06)30 mΩ MAX.

耐电压(EIA-364-20) NO DISCHARGE,
FLASHOVER OR BREAKDOWN
AT 500 V/AC 1MINUTE.

4.工作温度:-40℃ to +85℃

RECOMMENDED P.C.B HOLE LAYOUT
COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

1	TMDS Data2+	11	TMDS Clock Shield
2	TMDS Data2 Shield	12	TMDS Clock-
3	TMDS Data2-	13	CEC
4	TMDS Data 1+	14	Reserved (N.C)
5	TMDS Data 1 Shield	15	SCL
6	TMDS Data 1-	16	SDA
7	TMDS Data 0+	17	DDC/CEC Ground
8	TMDS Data 0 Shield	18	+5V Power
9	TMDS Data 0-	19	Hot Plug Detect
10	TMDS Clock+		

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
.X±0.35	X.*± 5°	APR.	Alex	TITLE: HDMI A TYPE 版本	
.XX±0.25	.X*± 3°	CHK.	Jack	DWG NO. XY-HDMI-19P	
.XXX±0.15	.XX*± 1°	DRA.	Can	PROJ.	CUSTOMER DRAWING
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A