










标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

| Pin | DIM A | DIM B | DIM C | DIM D |
|-----|-------|-------|-------|-------|
| 2   | 2.50  | 7.20  | 5.70  | 3.00  |
| 3   | 5.00  | 9.70  | 8.20  | 4.40  |
| 4   | 7.50  | 12.20 | 10.70 | 4.80  |
| 5   | 10.00 | 14.70 | 13.20 | 4.80  |
| 6   | 12.50 | 17.20 | 15.70 | 4.80  |
| 7   | 15.00 | 19.70 | 18.20 | 4.80  |
| 8   | 17.50 | 22.20 | 20.70 | 4.80  |
| 9   | 20.00 | 24.70 | 23.20 | 4.80  |
| 10  | 22.50 | 27.20 | 25.70 | 4.80  |
| 11  | 25.00 | 29.70 | 28.20 | 4.80  |
| 12  | 27.50 | 32.20 | 30.70 | 4.80  |
| 13  | 30.00 | 34.70 | 33.20 | 4.80  |
| 14  | 32.50 | 37.20 | 35.70 | 4.80  |
| 15  | 35.00 | 39.70 | 38.20 | 4.80  |
| 16  | 37.50 | 42.20 | 40.70 | 4.80  |



## SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperature Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltage: 1000V AC/minute
- 7.Material: Wafer PA66  
PIN Brass Tin-plated

|    |    |      |       |    |
|----|----|------|-------|----|
| 1  | 外壳 | PA66 | 白色    |    |
| 序号 | 品名 | 材质   | 电镀/颜色 | 备注 |



深圳市虹成电子有限公司

|               |               |
|---------------|---------------|
| 品名<br>TITLE   | 胶壳            |
| 料号<br>PART NO | HC-XA2. 54-2Y |

GENERAL TOLERANCES  
(UNLESS SPECIFIED)比 例  
SCALE

1:1

X±0.25 X'±2'

单 位  
UNIT

MM

X±0.25 X'±1'

张 数  
PART NO

1 OF 1

.XX±0.15 .XX'±0.5'

版 本  
REV

A

.XXX±0.10 .XXX'±0.5'

制 图  
DRAW审 核  
CHECKED

AhYe

夏操云

赵亮亮

