




| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|-------------|---------------------------------|---------------|-------------|----------------|
|             |                                 |               |             |                |
|             |                                 |               |             |                |

| PIN | 尺寸 (mm) |       |       |
|-----|---------|-------|-------|
|     | A       | B     | C     |
| 02  | 2.54    | 5.08  | 2.25  |
| 03  | 5.08    | 7.62  | 4.79  |
| 04  | 7.62    | 10.16 | 7.33  |
| 05  | 10.16   | 12.70 | 9.87  |
| 06  | 12.70   | 15.24 | 12.41 |
| 07  | 15.24   | 17.78 | 14.95 |
| 08  | 17.78   | 20.32 | 17.49 |
| 09  | 20.32   | 22.86 | 20.03 |
| 10  | 22.86   | 25.40 | 22.57 |
| 11  | 25.40   | 27.94 | 25.11 |
| 12  | 27.94   | 30.48 | 27.65 |
| 13  | 30.48   | 33.02 | 30.19 |
| 14  | 33.02   | 35.56 | 32.73 |
| 15  | 35.56   | 38.10 | 35.27 |
| 16  | 38.10   | 40.64 | 37.81 |

SPECIFICATIONS  
1.Current Rating: 4A AC, DC  
2.Voltage Rating: 250V AC, DC  
3.Temperatuer Range: -25°C~+85°C  
4.Contact Resistance: 20mΩ Max  
5.Insulation Resistance: 1000MΩ Min  
6.Withstanding Voltang: 1000V AC/minute  
7.Material: Wafer Nylon66  
PIN Brass Tin-plated

| 2   | 插针  | 铜    | 镀锡    |     |
|-----|-----|------|-------|-----|
| 1   | 基座  | PA66 | 米色    |     |
| 序 号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |

|                                          |             |                |                |                |      |
|------------------------------------------|-------------|----------------|----------------|----------------|------|
|                                          | 深圳市虹成电子有限公司 |                | 品 名<br>TITLE   | 针座             |      |
|                                          |             |                | 料 号<br>PART NO | HC-XH2510-2A-M |      |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED) |             | 比 列<br>SCALE   | 1:1            |                |      |
| X±0.25                                   | X'±2'       | 单 位<br>UNIT    | MM             | 制 图<br>DRAW    | AhYe |
| .X±0.20                                  | .X'±1'      | 张 数<br>PART NO | 1 OF 1         | 审 核<br>CHECKED | 夏操云  |
| .XX±0.15                                 | .XX'±0.5'   | 版 本<br>REV     | A              | 批 准<br>APPROVE | 赵亮亮  |
| .XXX±0.10                                | .XXX'±0.5'  |                |                |                |      |