

SIMATIC S7-400H, 同步模块 V6 用于转接电缆, 最长 10m



输入电流	
耗用电流, 最大值	220 mA
功率损失	
功率损失, 典型值	0.77 W
尺寸	
宽度	13 mm
高度	14 mm
深度	58 mm
重量	
重量, 约	14 g
分类	

	版本	分类
eClass	14	27-24-22-08
eClass	12	27-24-22-08
eClass	9.1	27-24-22-08
eClass	9	27-24-22-08
eClass	8	27-24-22-08
eClass	7.1	27-24-22-08
eClass	6	27-24-22-08
ETIM	10	EC001423
ETIM	9	EC001423
ETIM	8	EC001423
ETIM	7	EC001423
IDEA	4	3564
UNSPSC	15	32-15-17-05

认可 / 证书
General Product Approval



[Miscellaneous](#)



[China RoHS](#)



[KC](#)

General Product Approval	For use in hazardous locations
--------------------------	--------------------------------



FM



For use in hazardous locations

Maritime application



[Type Examination Certificate](#)



Maritime application

Environment

[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)



上一次修改：

2025/4/30