





标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE
A0	/	编号尺寸“B”修改	2024.12.16	ZLL

编号



尺寸 (mm)

编号	尺寸 (mm)	
	A	B
2X1AW	—	6.10
2X2AW	3.00	9.10
2X3AW	6.00	12.10
2X4AW	9.00	15.10
2X5AW	12.00	18.10
2X6AW	15.00	21.10
2X7AW	18.00	24.10
2X8AW	21.00	27.10
2X9AW	24.00	30.10
2X10AW	27.00	33.10
2X11AW	30.00	36.10
2X12AW	33.00	39.10



SPECIFICATIONS

- 1.Current Rating: 5A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material: Wafer PA66 Black
PIN Brass Tin-plated



PCB LAYOUT

2	插针	铜	镀锡	
1	基座	PA66	黑色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-5557-MX3.0-2x8AW

GENERAL TOLERANCES
(UNLESS SPECIFIED)比列
SCALE

1:1

单位
UNIT

MM

张数
PART NO

1 OF 1

版本
REV

A

制图
DRAW审核
CHECKED批准
APPROVE

AhYe

夏操云

赵亮亮

