

标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

编号

尺寸 (mm)

A

B

2X01

4.20

5.60

2X02

8.40

9.80

2X03

12.60

14.00

2X04

16.80

18.20

2X05

21.00

22.40

2X06

25.20

26.60

2X07

29.40

30.80

2X08

33.60

35.00

2X09

37.80

39.20

2X10

42.00

43.40





2X11

46.20

47.60


2X12

52.30



## SPECIFICATIONS

- 1.Current Rating: 7A AC, DC
- 2.Voltage Rating: 600V AC, DC
- 3.Temperatuer Range: -25℃~+85℃
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material: Wafer PA66  
PIN Brass Tin-plated



|    |    |      |       |    |
|----|----|------|-------|----|
| 1  | 胶壳 | PA66 | 本色    |    |
| 序号 | 品名 | 材质   | 电镀/颜色 | 备注 |



深圳市虹成电子有限公司

品 名  
TITLE

胶壳

料 号  
PART NO

HC-JK-5557-2x4Y

GENERAL TOLERANCES  
(UNLESS SPECIFIED)比 列  
SCALE

1:1



X.±0.25 X.±2°

单 位  
UNIT

MM

制 图  
DRAW

AhYe

.X±0.20 .X°±1°

张 数  
PART NO

1 OF 1

审 核  
CHECKED

夏操云

.XX±0.15 .XX°±0.5°

版 本  
REV

A

批 准  
APPROVE

赵亮亮

.XXX±0.10 .XXX°±0.5°

