







标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE



No. of Contacts	DIM A	DIM B	DIM C
2	2.5	10.0	6.20
3	5.0	12.5	8.70
4	7.5	15.0	11.20
5	10.0	17.5	13.70
6	12.5	20.0	16.20





2*8 (含8Y) 以下

SPECIFICATIONS

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: PA66



2*4Y



2*5Y-2*8Y

1	胶壳	PA66	白色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	胶壳
料号 PART NO	HC-XA2. 54-2x6Y

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 列
SCALE

1:1



X.±0.25

X.*±2"

单 位
UNIT

MM

制 图
DRAW

AhYe

.X±0.25

.X.*±1"

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

.XX±0.15

.XX.*±0.5"

版 本
REV

A

批 准
APPROVE

赵亮亮

.XXX±0.10

.XXX.*±0.5"

