




NOTE:1

1. ELECTRICAL CHARACTERISTICS:
1.1 CURRENT RATING: 0.5A MAX.
1.2 IMPEDANCE:50OHM NOMINAL.
2. MECHANICAL CHARACTERISTICS:
2.1 OPERATING TEMP. -40°~90°
2.2 VEWR UP TO 3GHz:1.3MAX.
3GHz TO 6GHz:1.4MAX.
2.3 DURABILITY:30CYCLES



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

NOTE:2

- 1.HOUSING MATERIAL: LCP, NATURE, UL94V-0.
2.TERMINAL MATERIAL: COPPER ALLOY (C2680),
3.SHELL MATERIAL: COPPER ALLOY (C5191),

3	GROUND CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
2	INNER CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
1	HOUSING	1	LCP UL94V-0		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARK

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: RF BOARD END CONNECTOR,FIRST GENERATION		
.X ± 0.35	X.* $\pm 5^{\circ}$	Alex	DWG NO. XY-IPEX1		
.XX ± 0.25	.X.* $\pm 3^{\circ}$	Jack	PROJ.  CUSTOMER DRAWING		
.XXX ± 0.15	.XX.* $\pm 1^{\circ}$	Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A