




标记
MARKECN编号/变更内容
ECN NO/DEFINITION修改
REVISE日期
DATE核准
APPROVE

芯数	A	B	C
2	2.0	8.0	4.8
3	4.0	10.0	6.8
4	6.0	12.0	8.8
5	8.0	14.0	10.8
6	10.0	16.0	12.8
7	12.0	18.0	14.8
8	14.0	20.0	16.8
9	16.0	22.0	18.8
10	18.0	24.0	20.8
11	20.0	26.0	22.8
12	22.0	28.0	24.8
13	24.0	30.0	26.8
14	26.0	32.0	28.8
15	28.0	34.0	30.8
16	30.0	36.0	32.8



技术要求:

额定电流: 2.0A AC,DC

额定电压: 250V AC,DC

温度范围: -25℃~85℃

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ


耐压: 800V/min

材料:


塑胶 LCP, 米色

插针 黄铜, 镀锡

焊片 黄铜, 镀锡



2PIN



PCB LAYOUT

2	插针	铜	镀锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HC-HY2.0-6PLT

GENERAL TOLERANCES
(UNLESS SPECIFIED)比列
SCALE

1:1

X.±0.30 X.±5°
.X±0.25 .X±3°
.XX±0.20 .XX±1°

单位
UNIT
张数
PART NO
版本
REV

MM
1 OF 1
A

制图
DRAW
审核
CHECKED
批准
APPROVE

AhYe
夏操云
赵亮亮

