




标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE




| No. of<br>Contacts | DIM A | DIM B | DIM C |
|--------------------|-------|-------|-------|
| 2                  | 2.5   | 5.7   | 3.0   |
| 3                  | 5.0   | 8.2   | 4.0   |
| 4                  | 7.5   | 10.7  | 5.0   |
| 5                  | 10.0  | 13.2  | 7.5   |
| 6                  | 12.5  | 15.7  | 10.0  |
| 7                  | 15.0  | 18.2  | 12.5  |
| 8                  | 17.5  | 20.7  | 12.5  |
| 9                  | 20.0  | 23.2  | 12.5  |
| 10                 | 22.5  | 25.7  | 12.5  |
| 11                 | 25.0  | 28.2  | 12.5  |
| 12                 | 27.5  | 30.7  | 12.5  |
| 13                 | 30.0  | 33.2  | 12.5  |
| 14                 | 32.5  | 35.7  | 12.5  |
| 15                 | 35.0  | 38.2  | 12.5  |
| 16                 | 37.5  | 40.7  | 12.5  |



2PIN



3PIN



## 技术要求:

额定电流: 3.0A AC,DC

额定电压: 250V AC,DC

温度范围: -25°C~85°C

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ

耐 压: 1000V/min

材 料: PA66, 白色

|    |     |      |       |     |
|----|-----|------|-------|-----|
| 1  | 胶壳  | PA66 | 白色    |     |
| 序号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |




深圳市虹成电子有限公司

|                |                  |
|----------------|------------------|
| 品 名<br>TITLE   | 胶壳               |
| 料 号<br>PART NO | HC-XHB2. 54-7Y-L |

GENERAL TOLERANCES  
(UNLESS SPECIFIED)比 列  
SCALE

1:1



|          |        |
|----------|--------|
| X.±0.30  | X.±5°  |
| .X±0.25  | .X±3°  |
| .XX±0.20 | .XX±1° |

|                |        |
|----------------|--------|
| 单 位<br>UNIT    | MM     |
| 张 数<br>PART NO | 1 OF 1 |
| 版 本<br>REV     | A      |

|                |      |
|----------------|------|
| 制 图<br>DRAW    | AhYe |
| 审 核<br>CHECKED | 夏操云  |
| 批 准<br>APPROVE | 赵亮亮  |

