





电路图



PCB开孔

NOTES:

1.MECHANICAL:

- 1>.Operation force: 1000gf Max.
- 2>.Operation Temperature: -30°C to $+85^{\circ}\text{C}$.
- 3>.Storage Temperature: -40°C to $+85^{\circ}\text{C}$.
- 4>.Mechanical Life: 3000 cycles operations.
- 5>.Resistance to Soldering: $260\pm 5^{\circ}\text{C}$ for 3~5 Seconds.
- 6>.Please keep switch in "OFF" when welding.

2.MATERIAL:

- 1>.Base: UL94V-0 PBT Thermoplastic / Color:Black.
- 2>.COVER: UL94V-0 PBT Thermoplastic / Color:Red, Black, Blue.
- 3>.ACTUATOR: UL94V-0 PBT High Thermoplastic / Color: White.
- 4>.TERMINAL: Copper alloy with gold plating for 1.5u".

3.ELECTRICAL:

- 1>.Non-switching Rating: 100mA at 50VDC.
- 2>.Switching Rating: 25mA at 24VDC.
- 3>.Contact Resistance: Initial 50mΩ Max.
Contact Resistance: After life 100mΩ Max.
- 4>.Insulation Resistance: 100MΩ Min at 500VDC.
- 5>.Dielectric Strength: 500VAC for 60seconds.
- 6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

XY-DSWBNLH-I

(包装方式:T=Tube)

(开关位数:1位-----12位)

(平数开关)

5.PACKING: 121pcs/Tube, 6050pcs/Box.

位数	A
1	3.54
2	6.64
3	9.18
4	11.72
5	14.26
6	16.80
7	19.34
8	21.88
9	24.42
10	26.96
12	32.04

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: PRODUCT Family DS Series Pitch 2.54mm	
.X±0±0.05	X.*±0.*±0.5	CHK.	Jack	DWG NO. XY-DSWBNLH-T	
.XX±1±1.10	.X.*±5.*±1.0*	DRA.	Can	PROJ.	CUSTOMER DRAWING
.XXX±10±0.30	.XX.*±	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A