









标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

PIN

尺寸 (mm)

	A	B	C	D
02	0.80	3.04	3.80	1.90
03	1.60	3.84	4.60	2.70
04	2.40	4.64	5.40	3.50
05	3.20	5.44	6.20	4.30
06	4.00	6.24	7.00	5.10
07	4.80	7.04	7.80	5.90
08	5.60	7.84	8.60	6.70
09	6.40	8.64	9.40	7.50
10	7.20	9.44	10.2	8.30



PCB Layout

技术要求:

额定电流: 0.7A AC,DC

额定电压: 30V AC

温度范围: -40° C~+85° C

接触电阻: ≤0.03 Ω

绝缘电阻: ≥100M Ω

耐 压: 200V AC/min

2	接触	铜	镀锡	
1	基座	LCP	米色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-SURO. 8-6PWT

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1

单 位
UNIT

MM

制 图
DRAW审 核
CHECKED批 准
APPROVE

X.±0.30

X.±5°

.X±0.25

.X±3°

.XX±0.20

.XX±1°

张 数
PART NO

1 OF 1

版 本
REV

A

夏操云

赵亮亮



AhYe

夏操云

赵亮亮

