

标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE
A0	/	编号尺寸“B”修改	2024.12.16	ZLL





编号

尺寸 (mm)

A



B

2X1AW	—	—	6.10
2X2AW	3.00	—	9.10
2X3AW	6.00	—	12.10
2X4AW	9.00	—	15.10
2X5AW	12.00	—	18.10
2X6AW	15.00	—	21.10
2X7AW	18.00	—	24.10
2X8AW	21.00	—	27.10
2X9AW	24.00	—	30.10
2X10AW	27.00	—	33.10
2X11AW	30.00	—	36.10
2X12AW	33.00	—	39.10



SPECIFICATIONS

- 1.Current Rating: 5A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -25°C~+85°C
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 1500V AC/minute
- 7.Material: Wafer PA66 Black
PIN Brass Tin-plated



PCB LAYOUT

2	插针	铜	镀锡	
1	基座	PA66	黑色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品 名 TITLE	针座	
			料 号 PART NO	HC-5557-MX3.0-2x2AW	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X±0.25	X*±2°	单 位 UNIT	MM	制 图 DRAW	AhYe
.X±0.25	.X*±1°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.15	.XX*±0.5°	版 本 REV	A	批 准 APPROVE	赵亮亮
.XXX±0.10	.XXX*±0.5°				