










RoHS

Technical requirements


Characteristic impedance	50Ω
Frequency range	0-3GHZ
Contact resistance	
Inner conductor	≤3mΩ
Outer conductor	≤2mΩ
Insulated resistance	≥5000MΩ
Salt spray time	48H
Separation force	≥0.28N
Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc	



PCB.WELDING DRAWING (TOLERANCE:±0.05)



A-A



1	铜座	1	黄铜	镀金
2	尖头母针	1	黄铜	镀金
3	绝缘体	1	PTFE	
序号	名称	数量	材料	备注

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.30	X.°	±5°
.XX	±0.20	X.X°	±1°
.XXX	±0.10	X.XX°	±0.5°
MANUFACTURE DWG			



深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

PART NO.

HMT-SMA-KE-P001A

TITLE:

内孔 SMA 偏脚

DESIGN:

James

CHED:

Talen

APPD:

Sophia

CUSTOMER

SIZE

A4

UNITS

MM

SCALE

N:A

SHEET

1/1