




VER	MARK	PR. BY	DESCRIPTION	DATE

Technical requirements	
Characteristic impedance	50 Ω
Frequency range	0-6GHZ
Contact resistance	
Inner conductor	≤3mΩ
Outer conductor	≤2mΩ
Insulated resistance	≥5000MΩ
Salt spray time	48H
Separation force	≥0.28N
Appearance: no shift point burr scratch surface bright, no dirt, no deformation, etc	

1	半螺铜套	1	黄铜	镀金
2	母针	1	黄铜	镀金
3	绝缘体 1	1	PTFE	
4	铜座	1	黄铜	镀金
5	绝缘体 2	1	PTFE	
序号	名称	数量	材料	备注

GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X.X ±0.30	X.° ±5°	PART NO.	TITLE:
.XX ±0.20	X.X° ±1°	HMT-SMA-KWE-Z001A	内孔 SMA 弯头
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
			SCALE SHEET
			N:A 1/1