




VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table

PART NO	PIN	A	B
WF-XH2. 54-2PZZ	2	2.50	7.50
WF-XH2. 54-3PZZ	3	5.00	10.00
WF-XH2. 54-4PZZ	4	7.50	12.50
WF-XH2. 54-5PZZ	5	10.00	15.00
WF-XH2. 54-6PZZ	6	12.50	17.50
.....			
WF-XH2. 54-20PZZ	20	47.50	52.50

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面 镀底镍 30u"MIN, 再镀锡 80u"MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.X ±0.30	X.° ±5°	PART NO.	TITLE:	
.XX ±0.20	X.X° ±1°	WF-XH2.54-NPZZ	XH2.54MM 直针	
.XXX ±0.10	X.XX° ±0.5°	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
				N:A 1/1