




RoHs


VER	MARK	PR. BY	DESCRIPTION	DATE

PIN number variable size comparison table			
PART NO	PIN	A	B
WF-HA2. 54-2PWZ	2	2. 50	7. 50
WF-HA2. 54-3PWZ	3	5. 00	10. 00
WF-HA2. 54-4PWZ	4	7. 50	12. 50
WF-HA2. 54-5PWZ	5	10. 00	15. 00
WF-HA2. 54-6PWZ	6	12. 50	17. 50
.....			
WF-HA2. 54-20PWZ	20	47. 50	52. 50

- 技术要求:
1. 塑件材料:PA66 (UL-94V-0)
 2. 接触件:黄铜镀锡
 3. 接触电阻:≤10mΩ
 4. 绝缘电阻:≥100MΩ
 5. 额定电压:250V AC DC
 6. 额定电流:2. 0A AC DC
 7. 耐压:能承受1000V AC/Minute
 8. 工作温度:-25° ~+85°
 9. 可焊性试验:浸锡面积≥95%温度235^{+5°}_{-0°}, 时间2. 5±0. 5秒
 10. 铅和镉等六大有害物质含量要符合环保要求.

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面 镀底镍 30u~MIN, 再镀 锡 80u~MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES UNLESS SPECIFIED			
X.X	±0.30	X.°	±5°
.XX	±0.20	X.X°	±1°
.XXX	±0.10	X.XX°	±0.5°
MANUFACTURE DWG			

 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		TITLE: HA2.54MM 带扣 弯针		
PART NO. WF-HA2.54-NPWZ		CUSTOMER	SIZE A4	UNITS MM
DESIGN: James			SCALE	SHEET
CHED: Talen			N:A	1/1
APPD: Sophia				