




RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	新版发行			2025.12.06

导体位数	N	6
间距	P	0.5±0.07
总间距	Pt	2.5±0.08
总长度	L	100±2
边缘宽度	M	0.5±0.08
总宽度	W	3.5±0.08
线口长度	S1	4±0.5
线口长度	S2	4±0.5
补强板长度	B1	8±1.0
补强板长度	B2	8±1.0
接插端厚度	T1	0.3±0.03
线身厚度	T2	0.12±0.05
线口倾斜度	A	≤0.3
冲孔倾斜度	B	≤0.5
补强板厚度		0.225
补强板颜色		蓝色
上绝缘胶		0.043/ 印字20624
下绝缘胶		0.043/ 白色

注：P位及长度可根据客户需求定制

X.±0.50	X.°±	PART NO: 0.5-06-100-B-4488		XFCN 兴飞连接器	
.X±0.25	.X°±				
.XX±0.15	.XX°±	TITLE: FFC 0.5mm间距 06P L=100mm B型 金手指4x4 补强板8x8 异面 镀锡		0769-82001899	
.XXX±0.10	.XXX°±			www.xfconn.com	
UNITS:	mm			DWG NO: /	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN		APPD	Chen ZhiQiang		
		CHKD	Liu Wei	VIEW	
		DRAW	Chen HongJiang	SCALE	SHEET
		DATE	2025.12.06	NONE	1/1
					REV
					A1