








Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



P= With Post



默认 = W/O Post

SPECIFICATIONS

Rated Current:1.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Phosphor Bronze
Contact Plating:Au Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Ordering Information

PM 127 - * - N - S - * - ** - P

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
2-40Pin

Type
2=直针
8=弯针
S=公插
K=母插

Length (Plastic)
(mm)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

Post
(带柱)

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM	TOL	DRAWING				
			X. X	±0.30	审 核	产品名称	1.27双排 排母 贴片 塑高4.3	版本	A
			X. XX	±0.20	批 准	TITLE		REV.	
			X. XXX	±0.10	APPROVAL	产品料号	PM127-2-N-S-4.3-XX(L4.6)	单 位	mm
			Angle	±3.0°	SCALE	PART NO.		UNITS	
序号	变更内容	日期	投影		投 影	材 料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Projection			MATERIAL		SHEET	