







Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C

Contact Material:Copper Alloy

Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 260°C±5°C 5S

Ordering Information

PM 254 - * - N - Z - * - **

No.of Rows
1=Single Row
2=Dual Row

No.of Pins
2-40Pin

Type
Z=直针
B=弯针
S=带轴
NS=带轴

Length
(英寸)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	DRAWING				
					审 核				
			X. X	±0.30	CHECK				
			X. XX	±0.20	批 准	产品名称	2.54双排 直针 排母(塑高5.0)	版本	A
			X. XXX	±0.10	APPROVAL	TITLE		REV.	
1	初版发行				比 例	产品料号	PM254-2-N-Z-5.0-XX	单 位	mm
					SCALE	PART NO.		UNITS	
序号	变更内容	日期			投 影	材 料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Angle	±3.0°	Projection	MATERIAL		SHEET	