




RoHS

REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.09.03

- 技术要求:
- 1.打铜底0.5-1μm,镍2-2.5μm, 镀哑锡3-5μm。
 - 2.铆好后不得有松动现象。
 - 3.插脚尖部符合可焊性要求。
 - 4.螺纹需符合通止规/止针要求。
 - 5.螺纹扭矩：2.5Nm.
 - 6.额定电流：100A.

>30.±0.4	X.°±	PART NO: TTR66250205-1750		XFCN 兴飞连接器							
6-30±0.3	.X°±										
0-6±0.2	.XX°±	TITLE: PCB SOLDERING TERMINAL		0769-82001899							
ANGLES±1°	.XXX°±			www.xfconn.com							
UNITS:	mm	APPD Chen ZhiQiang		DWG NO: /							
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED.COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN											
							CHKD Liu Wei		VIEW		
							DRAW Chen HongJiang		SCALE	SHEET	REV
		DATE 2024.12.03		NONE	1/1	A1					

2	垫片		SPCC	1
1	插脚		H62 (Y2)	1
序号	名称	零件编号	材质	数量