




Part No.	Cable color
~088*1T~	GRAY
~088*2T~	BLACK

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	U. FL-LP-088HF(06)	CL331-0560-8-06	2	1.37 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT 1	DESCRIPTION OF REVISIONS DIS-D-00003261	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 18. 06. 21
HRS HIROSE ELECTRIC CO., LTD.			APPROVED : NK. NINOMIYA 17. 12. 01	DRAWING NO. U. FL-2LPHF6-088 * T-AC-L 1		
			CHECKED : MT. KANEKO 17. 12. 01			
			DESIGNED : MS. MATSUMOTO 17. 12. 01			
			DRAWN : MS. MATSUMOTO 17. 12. 01			