






MATING HEIGHT



RECOMMENDED PCB LAYOUT(TOP VIEW)

L B 3 1 3 3 - S * * P - W O R

PACKING: R: REEL
0: WITH POSITIONING POSTS
1: WITHOUT POSITIONING POSTS
COLOR: WHITE
S: SOCKET
PIN
PLATING: S: SN G: GOLD FLASH
HEIGHT: 33-3.35H,
1.0 PITCH
LXWCONN BTB CONNECTOR SERIES

Note:

Electrical

Current Rating: 0.5A

Voltage Rating: 150V AC

Contact Resistance: 50mΩ max(Initial), 75mΩ max(After)

Dielectric Withstanding Voltage: 250VAC

Insulation Resistance 500mega ohms min. at 100 VDC

Physical

Housing: thermoplastic, UL 94V-0 rated, in White Color

Contact: Copper alloy

Operating Temperature: -45°C to +125°C

PIN	A	B	C	D	E
9 PIN	8.3	3	4	7.1	0
11 PIN	9.3	4	5	8.1	0
13 PIN	10.3	5	6	9.1	0
15 PIN	11.3	6	7	10.1	0
17 PIN	12.3	7	8	11.1	0
19 PIN	13.3	8	9	12.1	4
21 PIN	14.3	9	10	13.1	5
23 PIN	15.3	10	11	14.1	6
25 PIN	16.3	11	12	15.1	7
31 PIN	19.3	14	15	18.1	10
41 PIN	24.3	19	20	23.1	15
51 PIN	29.3	24	25	28.1	20



连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS (SHENZHEN) CO., LTD






制图 (DR):	JERRY	品名 (TITLE):	DF9 1.0 BTB PLUG
审核 (CHKD):		料号 (PART NO):	LB3133-S**P-WOR
核准 (APPD):	TONG	比例 (SCALE):	1:1
	2024.02.22	单位 (UNITS):	mm
		张数 (SHEET):	1 OF 1
		图幅 (SIZE):	A4

RoHS Compliant 2013/05/EC



修订	修改摘要	签名	日期
SER	REVISION DESCRIPTION	SIGNATURE	DATE

一般公差	GENERAL TOLERANCE
.X	±0.35
.XX	±0.25
.XXX	±0.15
ANGLES	±0° 30'



LB3133-S**S-WOR

PACKING: R:REEL
0:WITH POSITIONING POSTS
1:WITHOUT POSITIONING POSTS
COLOR:WHITE
S: SOCKET
PIN
PLATING: S:SN G:GOLD FLASH
HEIGHT:33-3.35H,
1.0 PITCH
LXWCONN BTB CONNECTOR SERIES

Note:

Electrical

Current Rating:0.5A

Voltage Rating:150V AC

Contact Resistance:50mΩ max(Initial),75mΩ max(After)

Dielectric Withstanding Voltage:250VAC

Insulation Resistance 500mega ohms min. at 100 VDC

Physical

Housing:thermoplastic, UL 94V-0 rated,inWhite Color

Contact: Copper alloy

Operating Temperature:-45°C to +125°C

	A	B	C	D	E
9 PIN	8.3	3	4	7.1	0
11 PIN	9.3	4	5	8.1	0
13 PIN	10.3	5	6	9.1	0
15 PIN	11.3	6	7	10.1	0
17 PIN	12.3	7	8	11.1	0
19 PIN	13.3	8	9	12.1	4
21 PIN	14.3	9	10	13.1	5
23 PIN	15.3	10	11	14.1	6
25 PIN	16.3	11	12	15.1	7
31 PIN	19.3	14	15	18.1	10
41 PIN	24.3	19	20	23.1	15
51 PIN	29.3	24	25	28.1	20

LXW 连兴旺电子(深圳)有限公司
connectivity LXWCONN ELECTRONICS(SHENZHEN) CO., LTD

制图 (DR):	JERRY	品名(TITLE):	DF9 1.0 BTB SOCKET
审核 (CHKD):		料号(PART NO):	LB3133-S**S-WOR
核准 (APPD):	TONG	比例(SCALE):	1:1
	2024.01.03	单位(UNITS):	mm
		张数(SHEET):	1 OF 1
		图幅(SIZE):	A4

RECOMMENDED PCB LAYOUT(TOP VIEW)

RoHS
Compliant
2013/05/EC



一般公差
GENERAL TOLERANCE:
.X ±0.35
.XX ±0.25
.XXX ±0.15
ANGLES ±0° 30'

修订 SER	新板发行	JERRY	12/05/19'
修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE	版本 (REV)

