






RoHS Compliant



▼ 0.10
(19 TINES)



Technical drawing of a component with the following dimensions:

- Overall width: 14.50 ± 0.05
- Central slot width: 9.00
- Central slot pitch: 0.50 (PITCH)
- Central slot height: 0.30
- Side slot height: 2.70
- Side slot width: 0.90
- Vertical dimension: 2.00
- Radius: R0.45

RECOMMENDED PCB LAYOUT (T=1.60)
TOLERANCES UNLESS OTHERWISE
SPEC. ± 0.05

备注：

1. 材质：
 - 1-1 塑胶：LCP E475 UL94V-0, 颜色：黑色
 - 1-2 端子：黄铜 C2680-H
 - 1-3 铁壳：铁材 SPCC
2. 电镀：
 - 端子接触区域：镀金1u”.
 - 端子锡脚：镀雾锡 80u”Min.
 - 端子整个表面：镀镍 50u”Min.
 - 铁壳：镀光亮可焊镍100u”.
3. 电气性能：
 - 3-1 端子额定电流：0.5A
 - 3-2 耐电压：500V 交流电
 - 3-3 接触电阻：100mΩ Max
 - 3-4 绝缘阻抗：
 - 公母未对插绝缘阻抗100 兆欧最小
 - 公母对插后绝缘阻抗10 兆欧最小
4. 机械性能
4-1 插入力：4.5kgf MAX
4-2 拨出力：1.0~4.0kgf
5. 环境
温度范围：-25° C TO +85° C
6. 零件必须符合ROHS标准。
7. ▼ 符号为重点检验尺寸。

2	外壳	SPCC 麻面 T=0.50mm 电镀镍80μ"	1Pcs
1	MD主体	Molding主体~9.8*13.96*6.0mm~LCP~黑色 (0.5μ"金)	1Pcs
NO.	品名	规格	数量

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT

 联晟欣连接器（深圳）有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd.

UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	DESIGN	Andy	DATE	2014.12.24	TITLE: HDMI TYPE-A/F端子镀金0.5u'黑色 载带热封		
	CHECKED		DATE				
	APPROVED		DATE				
PART NO: LCK-HDMI-1001				REV: 04	SCALE: 1:1	UNIT: mm	
DRAWING NO:				SIZE: A4	SHEET: 1/1		◎