







CAD FILE:

**ROHS**



SWITCH+DC SOCKET TWO IN ONE TECHNICAL PARAMETERS

一、ROCKER SWITCH & SPECIFICATION




NOTES:

1. Rating: 6A 10A 125V 250V AC  
CQC 6A 250VAC  
6(8)A 250VAC  
8A/128A 250VAC T105/55  
UL CUL 10GPA 125VAC  
6GPA 250VAC T105/55  
VDE ENEC 6(4)A 250VAC T85/55  
KC 6(4)A 250VAC T85/55
2. Circuit Diagram: 2P ON-OFF/3P ON-OFF-ON
3. Terminal Strength:  $\geq 80N$
4. Electrical life:  $\geq 10000$  cycles
5. Withstand Voltage: Withstand Voltage: 1500VAC 1min  
Terminals to Button: 3000VAC 1min
6. Leakage Current: 1mA
7. Current resistance:  $\leq 50m\Omega$  (initial)
8. Insulation resistance:  $> 100M \Omega$
9. Body Material: NYLON 66 94V-2<sup>0</sup>

二、DC JACK & SPECIFICATION

NOTES:

1. Rating : DC 12V 30V, 1A 3A
2. Contact resistance :  $\leq 30m\Omega$
3. Insulation resistance :  $> 100M\Omega$
4. Withstand voltage : 500VAC
5. Insertion and extraction force : 3-20N
6. Electrical life :  $> 10,000$  cycles



8					TOLERANCE				
7					UNLESS SPECIFIED				
6					WITHIN 1.5mm : $\pm 0.1mm$	A	2012-9-25	初版	ZENQ. CHEN
5					OVER 1.5mm : $\pm 0.2mm$	ISSUE	DATE	DESCRIPTIONS OF REVISION	APPD.
4	CONTACT	SUS	1	Ag CLAD	TITLE : Rotary Switch			UNIT : mm	DRWG NO.: XB-RS-DC-16
3	CASE	PPA/BRASS SRTIP	1	BLACK/Ag PLATED	MODEL: XB-RS-DC-16 翘板开关+DC插座合一			SCALE: 5:1	DWN. JUN. YANG 2012-9-25
2	COVER	STEEL STRIP	1	Ni PLATED	东莞市溪榜电子有限公司 DONG GUAN XI BANG ELECTRONICS CO., LTD.			CHK'D	DONG. PANG 2012-9-25
1	KNOB	PPA	1	BLACK				APPD.	ZENQ. CHEN 2012-9-25
NO.	PARTS	MATERIALS	Q'TY	FINISH					