




1: 成品需做100%导通测试: 不得有短/断路及错位现象。
2: 导通阻抗: 2欧姆 MAX
3: 绝缘阻抗: 10欧姆 MIN
4: 测试电压: 300V DC
5: 产品符合ROHS+REACH标准。

① ② ③ ④ ⑤

- ① 系列 (Series No)
- ② PIN:02P-15P
- ③ 1: 单头;2: 双头同向; 3双头异向
- ④ 线长 (Line length) L:(可定制长度); (X): 末端镀锡长度单位:mm
- ⑤ 线规线色 (Wire gauge line color) A:(AWG24)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
BL (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)

									备注	new		2015/5/3	A	瀚源			
										ECN BO.	DESCRIPTION.	DATE.	REV.				
										DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER		SCALT: 1/2	SCALE: 3:1	
										Mikey	Tom	Jerry	PART NAME		XH2. 54-6P-1-200 (3)-24A-UL1007	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. X.x X.xx
3	端子	XH-T	镀锡端子					2	PCS				MODEL NAME	XH2. 54-6P-1-200 (3)-24A-UL1007		ANGULAIR	?
2	胶壳	XH2. 54-6Y	白色					1	PCS				3RD ANGLE PROJ	HanElectricity Co.,LTD			FILE.NO.
1	线材:	UL1007-24AWG	红白黄绿蓝黑	L=200MM	尾部破铜3.0mm	200MM	1.0/3.0T	2	PCS								
序号	产品料号	产品规格描述			初级长度	剥头长度	分线长度	数量	单位								