


P2
镀锡

P1
HY2.0-5Y

3.0±0.3MM	镀锡	P1	红
3.0±0.3MM	镀锡	P2	白
3.0±0.3MM	镀锡	P2	黄
3.0±0.3MM	镀锡	P2	绿
3.0±0.3MM	镀锡	P2	黑

HY2.0-XXP-X-XXX(X)-XXA-UL1007
① ② ③ ④ ⑤

- ① 系列 (Series No)
② PIN:02P-15P
③ 1: 单头;2: 双头同向; 3双头异向
④ 线长 (Line length) L:(可定制长度); (X): 末端镀锡长度单位:mm
⑤ 线规线色 (Wire gauge line color) A:(AWG26)

Circuit:R(red)/B (black) /Y (yellow) /G (green) /
BL (blue) /P (purple) /YR (orange) /W (white) /N(brown) /E(grey)

注意事项:

- 1: 成品需做100%导通测试: 不得有短/断路及错位现象。
2: 导通阻抗: 2欧姆 MAX
3: 绝缘阻抗: 10欧姆 MIN
4: 测试电压: 300V DC
5: 产品符合ROHS+REACH标准。

									new		2015/5/3		A		瀚源						
									ECN BO.		DESCRIPTION.		DATE.			REV.					
									DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1				
									Mikey	Tom	Jerry	PART NAME		HY2. 0-5P-1-100 (3)-26A-UL1007		UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. X.x X.xx ANGULAIR ? 3			
												MODEL NAME		HY2. 0-5P-1-100 (3)-26A-UL1007							
												3RD ANGLE PROJ		HanElectricity Co.,LTD						FILE.NO.	
3	端子	HY2. 0-T 镀锡端子																			
2	胶壳	HY2. 0-5Y 白色																			
1	线材:	UL1007-26AWG 红白黄绿黑 L=100MM 绝缘镀锡3.0mm					100MM	1.0/3.0T													
序号	产品料号	产品规格描述					切线长度	剥头长度	分线长度	数量	单位										