




NOTE

1. Material
Plunger: Brass C6801
Barrel: Brass C6801
Spring: SUS 304

2. Plating
Plunger: 1 micro-inch minimum Au over 50~100 micro-inch nickel
Barrel: 1 micro-inch minimum Au over 50~100 micro-inch nickel

3. Electrical
Rated current & voltage: DC 12V; 1.0A Max.
Contact resistance: 50 mohm maximum at normal working height(quiescence)

4. Mechanic
Spring force: 60g±20% at normal working height
Durability: 10,000 cycles(minimum)

5. To ensure the best usage, please operate it based on the working height
Based on the engineering drawings, shall not exceed the maximum allowed compression

6. To avoid arcing issue, The adaptor start to power supply after connector mated fully.

7. RoHS compliant product.

yiYUAN 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD	页码 (SHEET)	1/1	单位(UNIT): MM
	版本 (REV)	A1	比例(SCALE)
	日期 (DATE)	2021. 10. 12	
	设计 (DESIGN)	LUO	未注公差 TOLERANCE UNSPECIFIED
品名 (ITEM NO)	Ø2.0×10.5导电铜针编带	审核 (CHECKED)	ROGER LI
料号 (PART NO)	YTC1P-8025-01R	核准 (APPROVED)	ROC ZHAO
图号 (DWG NO)			
These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd.The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com			