




PH2. 0-XXP-X-XXX (X)-XXA-UL1007

- ① 系列 (Series No)
 - ② PIN:02P-15P
 - ③ 1: 单头;2: 双头同向; 3双头异向
 - ④ 线长 (Line length) L:(可定制长度); (X): 末端镀锡长度单位:mm
 - ⑤ 线规线色 (Wire gauge line color) A:(AWG26)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
 BL (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)

- 1: 成品需做100%导通测试: 不得有短/断路及错位现象。
2: 导通阻抗: 2欧姆 MAX
3: 绝缘阻抗: 10欧姆 MIN
4: 测试电压: 300V DC
5: 产品符合ROHS+REACH标准。

										备注	ECN BO.		new		2015/5/3		A		瀚源	
											DESCRIPTION.		DATE.		REV.					
											DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2	SCALE: 3:1		
3	端子	PH2. 0~T	镀锡端子				2	PCS			Mikey	Tom	Jerry	PART NAME	PH2. 0-2P-1-200 (3)-26A-UL1007	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. X.x X.xx		70.25 70.20 70.15
2	胶壳	PH2. 0~2Y	白色				1	PCS		MODEL NAME				PH2. 0-2P-1-200 (3)-26A-UL1007					ANGULAIR	73
1	线材:	UL1007-26AWG 红黑	L=200MM尾部线长3. 0mm	200MM	1. 0/3. 0T		2	PCS		3RD ANGLE PROJ				HanElectricity Co.,LTD					FILE.NO.	
序号	产品料号	产品名称描述			切线长度	剥头长度	分线长度	数量	单位											