


P2
镀锡

P1
HY2.0-6Y

3.0±0.3MM	镀锡	P1	红
3.0±0.3MM	镀锡	P2	白
3.0±0.3MM	镀锡	P2	黄
3.0±0.3MM	镀锡	P2	绿
3.0±0.3MM	镀锡	P2	蓝
3.0±0.3MM	镀锡	P2	黑

注意事项:

- 1: 成品需做100%导通测试: 不得有短/断路及错位现象。
- 2: 导通阻抗: 2欧姆 MAX
- 3: 绝缘阻抗: 10欧姆 MIN
- 4: 测试电压: 300V DC
- 5: 产品符合ROHS+REACH标准。

HY2.0-XXP-X-XXX(X)-XXA-UL1007

① ② ③ ④ ⑤

- ① 系列 (Series No)
- ② PIN:02P-15P
- ③ 1: 单头;2: 双头同向; 3双头异向
- ④ 线长 (Line length) L:(可定制长度);(X): 末端镀锡长度单位:mm
- ⑤ 线规线色 (Wire gauge line color) A:(AWG26)

Circuit:R(red)/B (black) /Y (yellow) /G (green) /
BL (blue) /P (purple) /YR (orange) /W (white) /N(brown)/E(grey)

									new		2015/5/3		A		瀚源						
									ECN BO.		DESCRIPTION.		DATE.				REV.				
									DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER		SCALT: 1/2			SCALE: 3:1				
									Mikey	Tom	Jerry	PART NAME		HY2. 0-6P-1-100 (3)-26A-UL1007		UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.		20.25	
												MODEL NAME		HY2. 0-6P-1-100 (3)-26A-UL1007				X.xx		20.15	
												3RD ANGLE PROJ		HanElectricity Co.,LTD						FILE.NO.	
3	端子	HY2. 0-T 镀锡端子							2	PCS											
2	胶壳	HY2. 0-6Y 白色							1	PCS											
1	线材:	UL1007-26AWG 红白黄绿蓝黑 L=100MM导体镀锡3.0mm					100MM	1. 0/3. 0T		2	PCS										
序号	产品料号	产品规格描述					切线长度	剥头长度	分线长度	数量	单位										