









标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE
			PIN NUMBER	SIGNAL NAME
			1	VBUS
			2	D-
			3	D+
			4	GND



3D VIEW



RECOMMENDER P.C.B. LAYOUT TOP VIEW
(COMPONENT SIDE TOLERANCE ±0.05)

规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voitage:
500 V AC AT Sea Levot
5. 绝缘阻抗: Lnsulation Resistance:
500MEGA ohms MIN

物理特性: Mechanical:

1. 插拔力: Cnnector Mate and Unmate Force
Mate force: 35 N (MAX)
Unmate force: 5-35 N
2. 耐久 (寿命): 1500 Cycles Min
3. 工作温度: -25° C - +70° C
4. 存储温度: -40° C - +85° C
5. 盐雾测试: 24H (不包含外壳铆合折弯处)

3	外壳	铁	镀镍	
2	接触	铜	镀金	
1	基座	PBT	白色	
序号	品名	材质	电镀/颜色	备注

	深圳市虹成电子有限公司		品 名 TITLE	USB座	
			料 号 PART NO	HC-USB2.0-L100-J	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X. xxx ±0.10 X. xx ±0.20 X. x ±0.30		单 位 UNIT	MM	制 图 DRAW	AhYe
ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
		版 本 REV	A	批 准 APPROVE	赵亮亮

