





REV.	ECN	DESCRIPTION	MDF'D	DATE
	—	新订图面		




参数：

1. 线数：20~30
2. 适用线规：AWG30#
3. 温度范围：-25 °C~85 °C
4. 额定电压/电流：30V/DC 0.5A
5. 接触电阻： $\leq 350\text{m}\Omega$
6. 绝缘电阻： $> 100\text{M}\Omega$
7. 耐压：30V
8. 胶壳材质：PA66



线束	尺寸 A	尺寸 B	尺寸 C
2	1.25	2.72	5.72
3	2.50	3.97	6.97
4	3.75	5.22	8.22
5	5.00	6.47	9.47
6	6.25	7.72	10.72
7	7.50	8.97	11.97
8	8.75	10.22	13.22
9	10.00	11.47	14.47
10	11.25	12.72	15.72
11	12.50	13.97	16.97
12	13.75	15.22	18.22
20	23.75	25.22	28.22

 韩下[®] HANXIA 深圳市韩下电子有限公司

 韩下 HANXIA 深圳市韩下电子有限公司		页码 (SHEET)	1	单位 (UNIT): MM	
		版本 (REV)	A1	比例 (SCALE) 1:	
		日期 (DATE)	2025.12.10		
		设计 (DESIGN)	黄彬	未注公差 TOLERANCE UNSPECIFIED	
		审核 (CHECKED)	张伟	> XX ±3 > X ±1 0. X ±0.20 0. XX ±0.15	
料号 (PART NO)			核准 (APPROVED)	罗小春	
品名 (ITEM NO)	HX 1.25WRS-4P ST 200mm 30AWG				
图号 (DWG NO)					