






1
RoHS Compliant



电 路 图




PCB. 焊接图

主要技术规格：

- 额定值: 50mA DC12V
- 接触电阻: $\leq 50\text{m}\Omega$
- 操作力: $250 \pm 40\text{gf}$
- 行程: $0.4 \pm 0.2\text{mm}$
- 绝缘电阻: $\geq 100\text{M}\Omega$
- 抗电强度: 250V 50HZ 1Min.
- 寿命: 100,000 Cycles

H	H
4.1	4.3
4.5	5.0
5.5	6.0
6.5	7.0
7.5	8.0
8.5	9.0
9.5	10.0



高度
H41: 4.1H
H45: 4.5H
H55: 5.5H
.....
H100: 10.0H

包装方式
L: 圆盘
S: 袋装
Y: 有柱
W: 无柱
克力
1: 180克力
2: 250克力

5	引脚、触点	黄铜	1	镀银
4	基座	PPA	1	耐温280°C
3	簧片	不锈钢	1	覆银
2	盖板	冷轧钢	1	/
1	按钮	PPA	1	耐温280°C (黑色)
序号	零件名称	材料规格	数量	备注

QUADRANT POINT TOP POINT INTERSECTION POINT	TP IP	 联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd	DATE: 2014.12.24	TITLE: TACRILE SWITCH
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN CHECKED APPROVED	DATE DATE DATE	
X. ± 0.25				
X.X ± 0.20				
X.XX ± 0.15				
ANGULAR $\pm 3^\circ$				
PART NO: LCK-TA054HXX-XXXX		REV: 04	SCALE: 1:1	UNIT: mm
DRAWING NO:		SIZE: A4	SHEET: 1/1	⊕