






RoHS Compliant




### 主要技术规格:

- 额定值: 50mA DC12V
- 接触电阻:  $\leq 50\text{m}\Omega$
- 操作力:  $250\pm 40\text{gf}$
- 行程:  $0.4\pm 0.2\text{mm}$
- 绝缘电阻:  $\geq 100\text{M}\Omega$
- 抗电强度: 250V 50HZ 1Min.
- 寿命: 100,000 Cycles



PCB. 焊接图



电 路 图

H	
3.1	3.5
4.3	5.2

联晟欣  
LCK  
产品类别  
TA:轻触开关

产品流水料号识别码

LCK-TA 053 HXX-X X X

高度

H43:3.1H

H45:3.5H

H43:4.3H

H52:5.2H

包装方式

L:圆盘

S:袋装

Y: 有柱

W: 无柱

克力

1: 180克力

2: 250克力

5	引脚、触点	黄铜	1	镀银
4	基座	PPA	1	耐温280°C
3	簧片	不锈钢	1	覆银
2	盖板	冷轧钢	1	/
1	按钮	硅胶	1	耐温280°C (蓝色)
序号	零件名称	材料规格	数量	备注

QUADRANT POINT (QP)  
TANGENCY POINT (TP)  
INTERSECTION POINT (IP)

联晟欣连接器(深圳)有限公司  
Lianshengxin Connector (Shenzhen) Co., Ltd

UNLESS OTHERWISE SPECIFIED, TOLERANCE:	DESIGN	Andy	DATE	2014.12.24	TITLE:
X. $\pm 0.25$					TACRILE SWITCH
X.x $\pm 0.20$					
X.xx $\pm 0.15$					
ANGULAR $\pm 3^\circ$					
PART NO: LCK-TA053HXX-XXXX	REV: 04	SCALE: 1:1	UNIT: mm		
DRAWING NO:	SIZE: A4	SHEET: 1/1			