




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 02 through 24 Circuits.

Mates with DL42004-Y Series Housing.


Material : Nylon UL94V-0 (2) .

1.14mm Square Pin.

Pin Material : Brass / Tin-Plated.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	5569-2x1P-AW	---	5.4	14	5569-2x7P-AW	25.2	30.6
4	5569-2x2P-AW	4.2	9.6	16	5569-2x8P-AW	29.4	34.8
6	5569-2x3P-AW	8.4	13.8	18	5569-2x9P-AW	33.6	39.0
8	5569-2x4P-AW	12.6	18.0	20	5569-2x10P-AW	37.8	43.2
10	5569-2x5P-AW	16.8	22.2	22	5569-2x11P-AW	42.0	47.4
12	5569-2x6P-AW	21.0	26.4	24	5569-2x12P-AW	46.2	51.6

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: 5569-AW		TITLE: 4.20 mm Pitch Wire To Board Connector	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Chen Quan Long	DATE:21/08/01	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:21/08/01		
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV. : A



REV.	REVISION DESCRIPTION	DATE	APPD
A	19.9调整为20	3.24	刘
B	整体公差优化, 挂勾结构优化	20.5.20	Wu

NOTES

Available in 02 through 30 Circuits.

Match with DL42002/DL42003/
DL42004 series housing

Material : Nylon UL94V-0(2).

Accepts DL42002-T Crimp Terminal.

Circuits	Product name	Dimension mm		Circuits	Product name	Dimension mm	
		A	B			A	B
2	DLL-5557-2Y	---	5.4	18	DLL-5557-18Y	33.6	39.0
4	DLL-5557-4Y	4.2	9.6	20	DLL-5557-20Y	37.8	43.2
6	DLL-5557-6Y	8.4	13.8	22	DLL-5557-22Y	42.0	47.4
8	DLL-5557-8Y	12.6	18.0	24	DLL-5557-24Y	46.2	51.6
10	DLL-5557-10Y	16.8	22.2	26	DLL-5557-26Y	50.4	55.8
12	DLL-5557-12Y	21.0	26.4	28	DLL-5557-28Y	54.6	60.0
14	DLL-5557-14Y	25.2	30.6	30	DLL-5557-30Y	58.8	64.2
16	DLL-5557-16Y	29.4	34.8				

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL42002 (DLL-5557) -Y	TITLE: 4.2mm Pitch Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Chen Quan Long	DATE:21/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:21/08/01	PART NO:
FINISH:		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		APPD:Ren An De	PAGE: 1/2
		DATE:21/08/01	UNITS: mm
			REV.: B

REV.	REVISION DESCRIPTION	DATE	APPD
B	2.6改2.9	2016.6.27	Wuhui
C	倒翅结构改为撕破式	2023.9.19	Wuhui

NOTES

Used in DL42002-Y or DL42008-YM Series Housing.





Accepts AWG #28~18 Wire Range.

Insulation O.D.=0.9~2.8mm.

Material : Phosphor Bronze .

Finish: Tin plated.

Thickness: 0.2 mm.



TYPE	Dimension mm				Qty/Reel	适用线规 AWG#
	A1	B1	A2	B2		
DLL-5556-T-02	2.0	2.5	1.5	1.5	6,500 PCS	24-28
DLL-5556-T	3.9	3.7	2.1	2.25	5,000 PCS	18-24

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X° : ± 2.0°	DL42002(DLL-5556)-T		4.20 mm Pitch Crimp Terminal	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:2021/9/27	PART NO:	
FINISH:		CHKD: Wu Hui	DATE:2021/9/27	SCALE: N/A	
DRAWING NO:		APPD:Ren An De	DATE:2021/9/27	UNITS: mm	PAGE: 1/2
				REV.: C	

REV.	REVISION DESCRIPTION	DATE	APPD
△	3. 2改2. 6	2010. 10. 26	LIU BING
△	2. 6改2. 9	2016. 6. 27	Wuhui

NOTES

Used in DL42002-Y or DL42008-YM Series Housing.




Accepts AWG #20~14 Wire Range.

Insulation O.D.=2.2~3.1mm.


Material : Phosphor Bronze .

Finish: Tin plated.


Thickness: 0.2 mm.



SECTION A-A



SECTION B-B



SECTION C-C

TYPE	Dimension mm				Qty/Reel	适用线规 AWG#
	A1	B1	A2	B2		
DLL-5556-T-04	4.1	4.4	3.1	3.5	3,500 PCS	14-18
DLL-5556-T-03	3.9	4.4	2.1	2.7	3,500 PCS	16-20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE: 4.20 mm Pitch Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°	DL42002(DLL-5556)-T		PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:2021/9/27	SCALE: N/A	
FINISH: _____		CHKD: Wu Hui	DATE:2021/9/27	PAGE: 2/2	
DRAWING NO:		APPD:Ren An De	DATE:2021/9/27	UNITS: mm	REV.: A