




装吸取盖示意图

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND

备注:

1.材质:

1.1 胶芯: LCP+30%G.F UL94V-0

1.2 端子: 高导铜C7025, T=0.15mm;

1.3 外壳: SUS304, T=0.30mm;

1.4 中夹片: SUS301, $T=0.15\text{mm}$;

2. 主要特性:

2.1 额定电流: 5A

2.2接触阻抗: 40mΩ MAX(初始值)

50mΩ MAX(测试后)

2.3绝缘阻抗: 100M Ω MIN

2.4耐压测试: 100V AC R.M.S.

2.6整体插入力: 5-20N 整体插入力: 5-20N (耐久后)

整体拔出力:8-20N 整体拔出力:6-20N (耐久后)

2.7耐久: 10000次

2.8耐高温: SMT回流焊(峰值 $260^{\circ}\pm 5^{\circ}$), 塑胶不能有起泡,

融胶等不良,变色,翘曲变形在公差范围以内;



2.9产品须做焊锡测试,粘锡面积达到95%以上;

3.0盐雾测试: 48H MIN

3.1 工作温度: $-30^{\circ}\text{C} \sim +85^{\circ}\text{C}$



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY :		DATE :		PART NAME:	
X.X ±0.30		陈一鸣		2014-02-23		USB TYPE C 母座24P 立贴H=9.3mm 带小脚	
X.XX ±0.25		CHECKED BY:		DATE :		PART NO.	
X.XXX ±0.15						HYCW643-USBC24-930B	
X.* ±2* X.X ±0.5*		马跃		2014-02-23		MOLD NO.	
							
		APPROVED BY:		DATE :			
UNIT: mm [inch]		邱敏		2014-02-23		HYC-2512121153	
SCALE:1:1		SIZE: A4				SHEET NO.	
						1 OF 1	